Rittal – The System.

Faster – better – everywhere.



CS 9828.550

CS Toptec

State: 11/3/2026 (Source: www.rittal.com/us-en)

CS 9828.550 - CS Toptec

Outdoor enclosure with 100 mm transport base/plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS8 frame is available for interior installation.





Features

Model No.	CS 9828.550
Version	With cut-out for outdoor climate control unit 5118.21 BTU/h
Product description	Outdoor enclosure with 100 mm transport base/plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS8 frame is available for interior installation.
Material	Housing frame: Stainless steel 1.4301 (AISI 304) Enclosure panels and base/plinth panels: Aluminum, AlMg3 Rain canopy: Aluminum
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035

Features

Supply includes	Double-walled outdoor housing, fully preconfigured Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027 Side panels left and right Rear panel Rain canopy Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear
Dimensions	Width: 800 mm Height: 1,200 mm Depth: 800 mm Width: 31.5 ″ Height: 47.2 ″ Depth: 31.5 ″
Type rating according to 508A	Type 1 Type 3R Type 12
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 3R NEMA 12
IK code	IK10
Note	All enclosure panels are double wall and grounded (external wall to internal wall) CS Toptec is the foundation for project solutions in the outdoor sector. It can be requested under these order numbers: For individual installations: 9774.099, for baying: 9774.005
Note on Model No.:	To close the cutout, a climate control unit or adapter plate is needed
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	81 kg
Gross weight	84 kg
Customs tariff number	94032080

Features

ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	CS TopTec enclosure WHD: 800x1200x800 mm with cut-out for outdoor climate control units 1.5 kW

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity