

Rittal – The System.

Faster – better – everywhere.



IT 9982.207

TS IT Pro

State: 7/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 9982.207 - TS IT Pro

TS IT Pro configured for ready deployment. Black. Enclosures are complete with depth adjustable 19" EIA rails, casters, cable management walls with dual PDU mounting, baying kit and locking front and rear perforated doors. Available in a range of sizes with or without sidewalls.



Features

| | |
|---------------------|--|
| Model No. | IT 9982.207 |
| Product description | Ships complete with perforated single front door and split rear doors keyed alike, leveling feet, casters, roof with brush baffle cable access channels, vertical cable walls with dual PDU mountings. |
| Material | Carbon steel |
| Surface finish | Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated |
| General color | RAL 9005 |
| Color | Interior installation: RAL 9005 Enclosure frame and panels: RAL 9005 |

Features

| | |
|--------------------------------------|---|
| Supply includes | Perforated single steel door at the front (surface area approx. 85% perforated) 130° quick release internal hinges Perforated steel door at the rear vertically divided (surface area approx. 85% perforated) 130° quick release internal hinges Enclosure frame TS 8 with doors and roof plate Front and rear comfort handles with push button keyed door lock Installed caster kits Leveling Feet Baying Brackets (4 X 24" and 4 X 600mm) M6 cage nuts (Package of 50) M6 mounting screws (Package of 50) Two moveable cable management walls with dual PDU mounting and cable manager cutouts |
| Dimensions | Width: 600 mm Height: 2,012 mm Depth: 1,200 mm Width: 23.6 " Height: 79.2 " Depth: 47.2 " |
| Installation height for components | 42 U |
| Note | The door-opening angle may vary depending on site requirements or applications without side panels |
| Distance between levels as delivered | 745 mm 29.3 " |
| Design of 19" mounting level(s) | Profile rails, 482.6 mm (19") |
| Design doors | Perforated front and rear |
| Packaging unit | 1 pc(s). |
| Gross weight | 226.001 lb |
| Customs tariff number | 9403200082 |

Approvals

Approvals

Approvals

UL