

Rittal – The System.

Faster – better – everywhere.



IT 9982.230

TS IT Pro racks, Shiploadable

State: 7/1/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 9982.230 - TS IT Pro racks, Shiploadable

TS IT Pro configured for ready deployment. Enclosures are complete with depth adjustable 19" EIA rails, casters, right and left cable management walls each with dual PDU mounting, baying kit and locking front and rear perforated doors. Robust packaging system designed for safe equipment integration, transportation, and on site deployment. Meets ISTA 3E standards. Available in a range of sizes with sidewalls.

Features

Model No.	IT 9982.230
Product description	TS IT Pro configured for ready deployment. Enclosures are complete with depth adjustable 19" EIA rails, casters, right and left cable management walls each with dual PDU mounting, baying kit and locking front and rear perforated doors. Robust packaging system designed for safe equipment integration, transportation, and on site deployment. Meets ISTA 3E standards. Available in a range of sizes with sidewalls.
Material	Carbon steel
General color	RAL 9005
Color	Black RAL 9005

Features

Supply includes	<p>Perforated single steel door at the front (85% perforated) 145° quick release security hinges</p> <p>Perforated steel door at the rear vertically divided (85% perforated) 145° quick release security hinges</p> <p>Roof cable access with brushed baffles</p> <p>Front and rear comfort handles with push button keyed door lock</p> <p>Preinstalled heavy-duty casters</p> <p>Leveling feet (Package of 4 shipped loose)</p> <p>Fully welded steel frame</p> <p>19" EIA rails printed with U markings on the front and back of each rail</p> <p>M6 cage nuts (Package of 50)</p> <p>M6 mounting screws (Package of 50)</p> <p>Two moveable cable management walls with dual PDU mounting and cable manager cutouts</p> <p>Half-height quick release locking sidewalls keyed to match door locks</p> <p>Engineered shock pallet for safe transportation of IT equipment</p> <p>Three piece rugged shell</p> <p>Included ramp for unloading on site</p>
-----------------	---

Dimensions	<p>Width: 600 mm</p> <p>Height: 2,279 mm</p> <p>Depth: 1,070 mm</p> <p>Width: 23.6 "</p> <p>Height: 89.7 "</p> <p>Depth: 42.1 "</p>
------------	---

Height units	48 U
--------------	------

Height units	48 U
--------------	------

Version	Pre-configured
---------	----------------

Design doors	Perforated front and rear
--------------	---------------------------

Customs tariff number	9403999040
-----------------------	------------
