

Rittal – The System.

Faster – better – everywhere.

► Ex enclosures Stainless steel, empty enclosure with hinged door – KE 9407.600

Date : 27.9.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Ex enclosures Stainless steel, empty enclosure with hinged door – KE 9407.600

created: 27.09.2020 build on www.rittal.com/si-sl



Product description

Applications:	Zone 1 and 2 or 21 and 22 to 94/9/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)
Material:	Enclosure: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Sheet steel
Surface finish:	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Protection category IP to IEC 60 529:	IP 66
Protection category NEMA:	NEMA 4X
Certificates:	IEC Ex PTB 09.0035U: yes PTB 02 ATEX 1082U: yes
Supply includes:	Enclosure Door Mounting plate
Basic material:	Stainless steel

Product features

Dimensions: Width: 760 mm

Height: 760 mm
Depth: 300 mm

Mounting plate:	Width: 704 mm Height: 730 mm
Number of cam locks:	2
Lock version:	Cam
Number of locks:	2
Lock insert:	3 mm double-bit
Packs of:	1 pc(s).
Weight/pack:	44,1 kg
EAN:	4028177138865
Customs tariff number:	94032080
ETIM 7.0:	EC002503
ETIM 6.0:	EC002503
eCl@ss 8.0/8.1:	27180502
eCl@ss 6.0/6.1:	27180502
Product description:	KEL Ex enclosure, WHD: 760x760x300 mm, Stainless steel 1.4301, with mounting plate, Empty enclosure with hinged door

Approvals

Approvals:	ATEX IEC Ex UL + C-UL
Certificates:	EAC Ex IEC
Declarations:	Manufacturer's declaration