

Rittal – The System.

Faster – better – everywhere.

PDU international, metered version – DK 7955.210

Date : Oct 1, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PDU international, metered version – DK 7955.210

created: 01.10.2020 build on www.rittal.com/uae-en



Discontinued article.

Product expires on: 30.06.2020 |||This item is being replaced by: 7979215

Product description

Design:	PDU, metered
Description:	Energy measurement per phase, i.e. output requirement of an entire IT rack. Thanks to the compact PDU, any IT rack is easily equipped with a professional power distribution system. The compact design allows simple assembly – with the TS IT rack, assembly is even tool-free. The OLED display shows the energy consumption. An integral Web server offers a direct network connection with extensive user administration functions. Redundant power is supplied from all phases and additionally via an existing Power-over-Ethernet network. The PDU offers extensive monitoring functions. Measurement accuracy of 1% guarantees a high level of reliability.
Material:	Aluminium section, black anodised
Protection category IP to IEC 60 529:	IP 20
Standards:	EN 60950-1
Directives:	EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU

Product features

Variant:	Measurement per phase
Sockets:	24 x IEC 320 socket C13 - Black 4 x IEC 320 socket C19 - Black

To fit:	Enclosure type: TS IT Height: ≥ 1800 mm
Dimensions:	Width: 44 mm Depth: 62 mm Length: 1225 mm
Infeeds:	Qty.: 1 Phases per infeed: 1~
Length of connection cable:	3 m
Ambient conditions:	Operating temperature: +0 °C...+45 °C Storage temperature: -25 °C...+70 °C Ambient humidity (non-condensing): 10 % - 95 %
Type of electrical connection:	CEE
Rated current (max.):	16 A
Packs of:	1 pc(s).
Weight/pack:	7 kg
Copper weight (kg per piece):	0
EAN:	4028177685284
Customs tariff number:	85369095
ETIM 7.0:	EC000330
ETIM 6.0:	EC000330
eCl@ss 8.0/8.1:	27142604
eCl@ss 6.0/6.1:	27142604
Product description:	DK PDU international, metered version, Energy measurement per phase, WLD: 44x1225x62 mm, 24xC13, 4xC19, black, CEE, 1~, 16 A
Approvals	
Certificates:	EAC
Declarations:	Declaration of conformity