

Rittal – The System.

Faster – better – everywhere.

► Edge Standalone Solutions EAC 2.6 & 5.8kW

Simplify the specification process for your standalone Edge application with Rittal's pre-engineered Edge Air Conditioner (EAC) platform designs. These integrated enclosure solutions are equipped with cooling, power, monitoring, fire suppression, and accessories.

Designed for unconditioned spaces, this single enclosure solution protects critical IT equipment against dust, water, fire, and intrusions.

The EAC Standalone Platform utilizes the Rittal Blue e+ wall-mounted air conditioner with highly efficient hybrid technology. The unit contains both an active cooling circuit with speed-regulated components for demand-based cooling and an integral heat pipe for passive cooling.



EAC Edge Standalone Platform

Pre-engineered solutions with minimal site preparation - unpack, install, deploy, and repeat	✓
Sealed to protect mission critical IT equipment from dust, dirt, and water	✓
Safety, security, stability - designed to maximize uptime	✓
Remote monitoring and control for locations with limited IT support infrastructure	✓

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



System Parameters

EAC 2.6kW

General Information	Model Number	EAC-26M	EAC-26S
	IT Load	2.6kW Max.; actual capacity based on application parameters.	
	System Equipment	1 IT enclosure, 1 Blue e+ cooling unit	
	System Dimensions	Sidewall mount AC: 42U/79" (H) x 44" (W) x 40" (D) Rear door mount AC: 42U/79" (H) x 32" (W) x 52" (D)	
	System Color	Light gray (RAL 7035)	

Base System

IT Enclosure	Type/Doors	42U enclosure with glass viewing front and solid rear doors	
	Dimensions	42U/79" (H) x 32" (W) x 40" (D)	
	Accessories	Cable Management, Base Gland Plate, Sidewalls, LED light	
	Roof	3 part multi-functional for cable entry	Solid
	Protection Category	To NEMA 12 / IP 55 except for cable management roof (sealing kit provided)	NEMA 12 / IP 55
Cooling	Type	Self-contained Blue e+ air conditioner with two cooling circuits: active refrigerant cycle and passive hybrid heat pipe technology. IoT Interface for remote monitoring.	
	Mounting Location	Sidewall. Rear door with additional components.	
	Dimensions	63" (H) x 18" (W) x 12" (D)	
	Input Voltage	Multi-voltage capabilities for global installations: 110-240V, 1~, 50-60Hz 380-480V, 3~, 50-60Hz	
	Refrigerant	R134a	
	Condensate	Integrated electric condensate evaporator	
Base	Base (Plinth)	4" raised base on IT enclosure for installation on slab floor	

Options

Power	UPS	1x - 120V, 1~, 3000VA/2880W, 2U	
	Rack PDU	1x - 120V, 30A, 1~, 2.8kW, Switched	
Monitoring	Environmental	Vandalism, temperature/humidity, leak. Additional sensors available.	
	Remote	Remote monitoring on web browser; alerts via SNMP and other protocols	
Security	Rack Access	Rack access control with PIN pad or card reader. Optional network camera	
Safety	Fire Suppression	In-rack 1U fire suppression system with Novec 1230; with start-up service. Sealing kit provided for roof brush strips	In-rack 1U fire suppression system with Novec 1230; with start-up service
Services	On-Site	Installation, configuring, start-up service, preventative maintenance	

System Parameters

EAC 5.8kW

General Information	Model Number	EAC-58M	EAC-58S
	IT Load	5.8kW Max.; actual capacity based on application parameters.	
	System Equipment	1 IT enclosure, 1 Blue e+ cooling unit	
	System Dimensions	42U/79" (H) x 48" (W) x 40" (D)	
	System Color	Light gray (RAL 7035)	

Base System

IT Enclosure	Type/Doors	42U enclosure with glass viewing front and solid rear doors	
	Dimensions	42U/79" (H) x 32" (W) x 40" (D)	
	Accessories	Cable Management, Base Gland Plate, Sidewalls, LED light	
	Roof	3 part multi-functional for cable entry	Solid
	Protection Category	To NEMA 12 / IP 55 except for cable management roof (sealing kit provided)	NEMA 12 / IP 55
Cooling	Type	Self-contained Blue e+ air conditioner with two cooling circuits: active refrigerant cycle and passive hybrid heat pipe technology. IoT Interface for remote monitoring.	
	Mounting Location	Sidewall	
	Dimensions	63" (H) x 18" (W) x 15" (D)	
	Input Voltage	380-480V, 3~, 50-60Hz	
	Refrigerant	R134a	
	Condensate	Integrated electric condensate evaporator	
Base	Base (Plinth)	4" raised base on IT enclosure for installation on slab floor	

Options

Power	UPS	1x - 208V, 1~, 8000VA/6900W, 6U	
	Rack PDU	2x - 208V, 20A, 1~, 3.3kW, Smart	
Monitoring	Environmental	Vandalism, temperature/humidity, leak. Additional sensors available.	
	Remote	Remote monitoring on web browser; alerts via SNMP and other protocols	
Security	Rack Access	Rack access control with PIN pad or card reader. Optional network camera	
Safety	Fire Suppression	In-rack 1U fire suppression system with Novec 1230; with start-up service. Sealing kit provided for roof brush strips	In-rack 1U fire suppression system with Novec 1230; with start-up service
Services	On-Site	Installation, configuring, start-up service, preventative maintenance	

Rittal North America LLC

Woodfield Corporate Center
 425 North Martingale Road, Suite 400 • Schaumburg, Illinois 60173 • USA
 Phone: 937-399-0500 • Toll-free: 800-477-4000
 Email: rittal@rittal.us • Online: www.rittal.com

US564-OS ■ 9/21

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

